

# Eaton NCGS237

Catalog Number: NCGS237

Eaton Crouse-Hinds series NCGS solar cord grip, Hole cable diameter: 7 mm, Nylon, 3 holes, 3/4", #12 AWG, #10 AWG, 1000V PV cable

## General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series NCGS solar cord grip	NCGS237
	UPC
	662277054546
Product Length/Depth	Product Height
2 in	1.5 in
Product Width	Product Weight
1.5 in	0.15 lb



Powering Business Worldwide

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### Ingress protection (IP) ratings

IP68

## Product specifications

### Trade size

3/4"

### Material

Nylon

### Number of holes

Three-hole

### Hole cable diameter

7 mm

### Wire type

1000V PV cable

### Wire size

#12 AWG

#10 AWG

## Resources

### Catalogs

[Crouse-Hinds series NCGS catalog page](#)

### Certification reports

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors Canadian certification](#)

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - NCGS237](#)