

Eaton NCGS497

Catalog Number: NCGS497

Eaton Crouse-Hinds series NCGS solar cord grip, Hole cable diameter: 7 mm, Nylon, 9 holes, 1-1/4", #12 AWG, #10 AWG, 1000V PV cable

General specifications



Photo is representative

| Product Name | Catalog Number |
|--|----------------|
| Eaton Crouse-Hinds series NCGS solar cord grip | NCGS497 |
| | UPC |
| | 662277054560 |
| Product Length/Depth | Product Height |
| 2.7 in | 2 in |
| Product Width | Product Weight |
| 2 in | 0.21 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

Ingress protection (IP) ratings

IP68

Product specifications

Trade size

1-1/4"

Material

Nylon

Number of holes

Nine-hole

Hole cable diameter

7 mm

Wire type

1000V PV cable

Wire size

#12 AWG

#10 AWG

Resources

Catalogs

[Crouse-Hinds series NCGS catalog page](#)

Certification reports

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors Canadian certification](#)

[NCG, NCGB and NCGS Non-metallic Portable Cord Connectors UL certification](#)

Specifications and datasheets

[Eaton Specification Sheet - NCGS497](#)