

Eaton NPJ6484

Catalog Number: NPJ6484

Eaton Crouse-Hinds series Arktite NPJ plug, 60A, Three-wire, four-pole, 0.75-1.07", 50-400 Hz, Style 2, Krydon fiberglass-reinforced polyester, 600 Vac/250 Vdc

General specifications



Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite NPJ plug	NPJ6484
	UPC 782274746159
Product Length/Depth	Product Height
9.5 in	4 in
Product Width	Product Weight
4 in	2.75 lb

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

60A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cord diameter

0.75-1.07"

Material

Krydon fiberglass-reinforced polyester

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds NPJ6484 3D drawing](#)

Catalogs

[Arktite Nonmetallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Nonmetallic Plugs, Receptacles and Connectors UL certification \(NPJ, NPQ and NPR\)](#)

Installation instructions

[IF 865 - NPJ Series Arktite Heavy Duty Plug, Model M1, Style 2, 30, 60, 100 Amp](#)

Specifications and datasheets

[Eaton Specification Sheet - NPJ6484](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)