

# Eaton NPQ338

Catalog Number: NPQ338

Eaton Crouse-Hinds series Arktite NPQ motor plug, 30A, Two-wire, three-pole, 50-400 Hz, Style 2, Krydon fiberglass-reinforced polyester, 600 Vac/250 Vdc



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite NPQ motor plug	NPQ338
	UPC
	782274255583
Product Length/Depth	Product Height
2.94 in	3.38 in
Product Width	Product Weight
3.38 in	1.25 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

30A

### Grounding type

Style 2

### Configuration

Two-wire, three-pole

### Material

Krydon fiberglass-reinforced polyester

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds NPQ338 3D drawing](#)

### Catalogs

[Arktite Nonmetallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Nonmetallic Plugs, Receptacles and Connectors UL certification \(NPJ, NPQ and NPR\)](#)

### Installation instructions

[IF 867 - NPQ Series Heavy Duty Motor Plug, Model M1, Style 2, 30, 60, 100 Amp](#)

### Specifications and datasheets

[Eaton Specification Sheet - NPQ338](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)