

Eaton NPR3364

Catalog Number: NPR3364

Eaton Crouse-Hinds series Arktite NPR connector, 30A, Two-wire, three-pole, 0.70-0.85", 50-400 Hz, Style 2, Krydon fiberglass-reinforced polyester, 600 Vac/250 Vdc

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite NPR connector	NPR3364
	UPC
	782274254135
Product Length/Depth	Product Height
8.88 in	2.56 in
Product Width	Product Weight
2.56 in	1 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

30A

Grounding type

Style 2

Configuration

Two-wire, three-pole

Cord diameter

0.70-0.85"

Material

Krydon fiberglass-reinforced polyester

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds NPR3364 3D drawing](#)

Catalogs

[Arktite Nonmetallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Nonmetallic Plugs, Receptacles and Connectors UL certification \(NPJ, NPQ and NPR\)](#)

Installation instructions

[IF 868 - NPR Series Heavy Duty Connector, Model M1, Style 2, 30, 60, 100 Amp](#)

Specifications and datasheets

[Eaton Specification Sheet - NPR3364](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)