

Eaton NR1042

Catalog Number: NR1042

Eaton Crouse-Hinds series Arktite NR receptacle, 100A, Three-wire, four-pole, 50-400 Hz, Style 2, Krydon fiberglass-reinforced polyester, Snap-on cap/spring door, 600 Vac/250 Vdc



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite NR receptacle	NR1042
	UPC
	782274255552
Product Length/Depth	Product Height
5.75 in	4.25 in
Product Width	Product Weight
4.25 in	3.75 lb

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

100A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Receptacle style

Snap-on cap/spring door

Material

Krydon fiberglass-reinforced polyester

Voltage rating

600 Vac/250 Vdc

Frequency rating

50 to 400 Hz

Resources

3D CAD drawing package

[Eaton Crouse-Hinds NR1042 3D drawing](#)

Catalogs

[Arktite Nonmetallic Plugs, Receptacles and Connectors catalog page](#)

Certification reports

[Arktite Nonmetallic Plugs, Receptacles and Connectors UL certification \(NR\)](#)

Specifications and datasheets

[Eaton Specification Sheet - NR1042](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)