

# Eaton NR642

Catalog Number: NR642

Eaton Crouse-Hinds series Arktite NR receptacle, 60A, Three-wire, four-pole, 50-400 Hz, Style 2, Krydon fiberglass-reinforced polyester, Snap-on cap/spring door, 600 Vac/250 Vdc



## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series Arktite NR receptacle	NR642
	UPC
	782274746012
Product Length/Depth	Product Height
4.5 in	4.25 in
Product Width	Product Weight
4.25 in	2.95 lb

## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

60A

### Grounding type

Style 2

### Configuration

Three-wire, four-pole

### Receptacle style

Snap-on cap/spring door

### Material

Krydon fiberglass-reinforced polyester

### Voltage rating

600 Vac/250 Vdc

### Frequency rating

50 to 400 Hz

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds NR642 3D drawing](#)

### Catalogs

[Arktite Nonmetallic Plugs, Receptacles and Connectors catalog page](#)

### Certification reports

[Arktite Nonmetallic Plugs, Receptacles and Connectors UL certification \(NR\)](#)

### Specifications and datasheets

[Eaton Specification Sheet - NR642](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)