

Eaton NT20P11F10CUNV

Catalog Number: NT20P11F10CUNV

K-Factor Transformer, Ventilated, K-13, Single-phase, PV: 240 X 480V, Taps: 1 at +5% FCAN, 2 at -5% FCBN X 2 at +2.5% FCAN, 4 at -2.5% FCBN, SV: 120/240V, 115°C, 10 kVA, Cu windings , Elec. Shield, Frame: 816N



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Totally enclosed non-ventilated transformer	NT20P11F10CUNV
	UPC
	786680071416

Product Length/Depth	Product Height
18.39 in	31.3 in

Product Width	Product Weight
22.89 in	302 lb

Warranty	Certifications
-----------------	-----------------------

Eaton Selling Policy 25-000, one (1) year UL Listed

from the date of installation of the

Product or eighteen (18) months from the

date of shipment of the Product,

whichever occurs first.

[Catalog Notes](#)

Totally enclosed non-ventilated



Powering Business Worldwide

Physical Attributes

Coil material

Copper

Design

K-13

Frame

816N

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at +2.5% FCAN, 4 at -2.5% FCBN

Type

Non-ventilated transformer

Performance Ratings

Frequency rating

60 Hz

Kva Rating

10 kVA

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Miscellaneous

Special features

Electrostatically shielded

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - NT20P11F10CUNV](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)