

Eaton OLI361FDJA-00VT

Catalog Number: OLI361FDJA-00VT

Eaton OLI Switch: 30A/3P, 600VAC Fusible(J), NEMA Type 12/3R
- Includes both voltage Indicator and Voltage Tester on LOAD Side

General specifications



Photo is representative

Product Name	Catalog Number
Eaton oem line isolation switch	OLI361FDJA-00VT
UPC	Product Length/Depth
786689211417	21.49 in
Product Height	Product Width
9.24 in	16.08 in
Product Weight	Certifications
40 lb	UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Number Of Poles

Three-pole

Type

OLI Switch

Performance Ratings

Amperage Rating

30A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Multimedia

[OEM Line Isolation Switch \(OLI\)](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI361FDJA-00VT](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia