

# Eaton OLI362FDJB-00VT

Catalog Number: OLI362FDJB-00VT

Eaton OLI Switch: 60A/3P, 600VAC Fusible(J), NEMA Type 12/3R  
- Includes both voltage Indicator and Voltage Tester on LINE and LOAD Side



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton oem line isolation switch	OLI362FDJB-00VT
<b>UPC</b>	<b>Product Length/Depth</b>
786689211394	21.49 in
<b>Product Height</b>	<b>Product Width</b>
9.24 in	16.08 in
<b>Product Weight</b>	<b>Certifications</b>
40 lb	UL Listed

## Physical Attributes

### Enclosure

NEMA 12, NEMA 3R

### Number Of Poles

Three-pole

### Type

OLI Switch

## Performance Ratings

### Amperage Rating

60A

### Fuse class provision

Class J fusible

### Voltage rating

600 V

## Resources

### Multimedia

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[ARMS Enclosed Circuit Breaker](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - OLI362FDJB-00VT](#)



Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)