

Eaton OLI362FDJC-0000

Catalog Number: OLI362FDJC-0000

Eaton OEM line isolation switch, 60 A, NEMA 12/3R, Galvanized steel, Class J, Fusible without neutral, Three-pole, Three-wire, 600 V, #14-#2 Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI362FDJC-0000
UPC	Product Length/Depth
786676034289	21.49 in
Product Height	Product Width
9.24 in	16.08 in
Product Weight	Certifications
40 lb	UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

60A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Multimedia

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[ARMS Enclosed Circuit Breaker](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI362FDJC-0000](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)