

Eaton OLI362FWJB-00VP

Catalog Number: OLI362FWJB-00VP

Eaton OEM line isolation switch, Two voltage portals, 60 A, NEMA 4X, 304 stainless steel, Class J fusible, Fusible without neutral, Three-pole, Three-wire, 600 V, #14-#2 Cu/Al



Photo is representative

General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton oem line isolation switch | OLI362FWJB-00VP |
| UPC | Product Length/Depth |
| 786676034388 | 21.49 in |
| Product Height | Product Width |
| 9.24 in | 16.08 in |
| Product Weight | Certifications |
| 40 lb | UL Listed |

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

60A

Fuse class provision

Class J fusible

Voltage rating

600 V

Miscellaneous

Special features

Two voltage portals

Resources

Multimedia

[OEM Line Isolation Switch \(OLI\)](#)

[ARMS Enclosed Circuit Breaker](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI362FWJB-00VP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)