

Eaton OLI364FDJA-0000

Catalog Number: OLI364FDJA-0000

Eaton OEM line isolation switch, 200 A, NEMA 12/3R, Galvanized steel, Class J, Fusible without neutral, Three-pole, Three-wire, 600 V, #6-300 kcmil Cu/Al



Photo is representative

General specifications

| | |
|---------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton oem line isolation switch | OLI364FDJA-0000 |
| UPC | Product Length/Depth |
| 786676034616 | 28.21 in |
| Product Height | Product Width |
| 9.24 in | 18.3 in |
| Product Weight | Certifications |
| 54 lb | UL Listed |

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

200A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI364FDJA-0000](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)