

Eaton OLI364FDJB-00VP

Catalog Number: OLI364FDJB-00VP

Eaton OEM line isolation switch, Two voltage portals, 200 A, NEMA 12/3R, Galvanized steel, Class J fusible, Fusible without neutral, Three-pole, Three-wire, 600 V, #6-300 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI364FDJB-00VP
UPC	Product Length/Depth
786676034647	28.21 in
Product Height	Product Width
9.24 in	18.3 in
Product Weight	Certifications
54 lb	UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

200A

Fuse class provision

Class J fusible

Voltage rating

600 V

Miscellaneous

Special features

Two voltage portals

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI364FDJB-00VP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)