

Eaton OLI364FDJB-ORNG

Catalog Number: OLI364FDJB-ORNG

Eaton OEM line isolation switch, 200 A, NEMA 12/3R, Galvanized steel, Class J, Fusible with no neutral, Three-pole, Three-wire, Painted Orange, 600 V, #6-300 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI364FDJB-ORNG
UPC	Product Length/Depth
786689243340	9.24 in
Product Height	Product Width
21.49 in	18.3 in
Product Weight	Certifications
54 lb	UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Enclosure material

Galvanized steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

200A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Multimedia

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI364FDJB-ORNG](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)