

Eaton OLI364FDJC-00VT

Catalog Number: OLI364FDJC-00VT

Eaton OLI Switch: 200A/3P, 600VAC Fusible(J), NEMA Type 12/3R - Includes both voltage Indicator and Voltage Tester on LINE Side



General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI364FDJC-00VT
UPC	Product Length/Depth
786689211486	28.21 in
Product Height	Product Width
9.24 in	18.3 in
Product Weight	Certifications
51 lb	UL Listed

Physical Attributes

Enclosure

NEMA 12, NEMA 3R

Number Of Poles

Three-pole

Type

OLI Switch

Performance Ratings

Amperage Rating

200A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Multimedia

[Double Up on Safety](#)

[ARMS Enclosed Circuit Breaker](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[Switching Devices Flex Center](#)

[OEM Line Isolation Switch \(OLI\)](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI364FDJC-00VT](#)



Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia