

# Eaton OLI365FDJA-00VP

Catalog Number: OLI365FDJA-00VP

Eaton OEM line isolation switch, Voltage portal, 400 A, NEMA 12/3R, Galvanized steel, Class J, Fusible without neutral, Three-pole, Three-wire, 600 V, (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Cu/Al



Photo is representative

## General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI365FDJA-00VP
UPC	Product Length/Depth
786676034692	50.15 in
Product Height	Product Width
9.24 in	21.3 in
Product Weight	Certifications
100 lb	UL Listed

## Physical Attributes

### Enclosure

NEMA 12, NEMA 3R

### Enclosure material

Galvanized steel

### Fuse configuration

Fusible without neutral

### Number Of Poles

Three-pole

### Number of wires

3

### Type

OEM line isolation switch

## Performance Ratings

### Amperage Rating

400A

### Fuse class provision

Class J fusible

### Voltage rating

600 V

## Miscellaneous

### Special features

Voltage portal

## Resources

### Multimedia

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[OEM Line Isolation Switch \(OLI\)](#)

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - OLI365FDJA-00VP](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)