

Eaton OLI365FWJA-00VP

Catalog Number: OLI365FWJA-00VP

Eaton OEM line isolation switch, Voltage portal, 400 A, NEMA 4X, 304 stainless steel, Class J fusible, Fusible without neutral, Three-wire, Three-pole, 600 V, (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI365FWJA-00VP
UPC	Product Length/Depth
786676034746	50.15 in
Product Height	Product Width
9.24 in	21.3 in
Product Weight	Certifications
100 lb	UL Listed

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class J fusible

Voltage rating

600 V

Miscellaneous

Special features

Voltage portal

Resources

Multimedia

[ARMS Enclosed Circuit Breaker](#)

[Double Up on Safety](#)

[OEM Line Isolation Switch \(OLI\)](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI365FWJA-00VP](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)