

Eaton OLI365FWJB-0000

Catalog Number: OLI365FWJB-0000

Eaton OEM line isolation switch, 400 A, NEMA 4X, 304 stainless steel, Class J fusible, Fusible without neutral, Three-pole, Three-wire, 600 V, (2)#1/0-(2)300 kcmil; or (1)#1/0-(1)750 kcmil Cu/Al



Photo is representative

General specifications

Product Name	Catalog Number
Eaton oem line isolation switch	OLI365FWJB-0000
UPC	Product Length/Depth
786676034753	50.15 in
Product Height	Product Width
9.24 in	21.3 in
Product Weight	Certifications
100 lb	UL Listed

Physical Attributes

Enclosure

NEMA 4X

Enclosure material

304 stainless steel

Fuse configuration

Fusible without neutral

Number Of Poles

Three-pole

Number of wires

3

Type

OEM line isolation switch

Performance Ratings

Amperage Rating

400A

Fuse class provision

Class J fusible

Voltage rating

600 V

Resources

Multimedia

[OEM Line Isolation Switch \(OLI\)](#)

[Eaton OEM Line Isolation Switch \(OLI\) Installation Video](#)

[ARMS Enclosed Circuit Breaker](#)

[Switching Devices Flex Center](#)

[Double Up on Safety](#)

Specifications and datasheets

[Eaton Specification Sheet - OLI365FWJB-0000](#)



Eaton Corporation plc

Eaton House

30 Pembroke Road

Dublin 4, Ireland

Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)