

# Eaton P60G11S0712

Catalog Number: P60G11S0712

Eaton 7.5 KVA Mini Power Center 1PH 600V-120/240V 12 spaces



Photo is representative

## General specifications

### Product Name

Eaton Mini-Power center

### Catalog Number

P60G11S0712

### UPC

786680225680

### Product Length/Depth

8.9 in

### Product Height

18 in

### Product Width

11.9 in

### Product Weight

125 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

NAFTA

### Certifications

CSA Certified

ANSI

IEEE Certified

UL Listed

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

284

### Insulation

180 °C

### Mounting

Wall Mount

### Tap size

2 at -5% FCBN

### Type

Mini-power center

### Wiring connection

M60G11E

## Performance Ratings

### Frequency rating

60 Hz

### kVA

7.5 kVA

### Kva Rating

7.50 kVA

### Phase

Single-phase

### Primary voltage

600 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

7.5 kVA

## Miscellaneous

### Modification 1

NEMA 3R

### Weathershield

Not required

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Multimedia

[Eaton's Transformer Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - P60G11S0712](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)