

Eaton PDD32K0175VFAN

Catalog Number: PDD32K0175VFAN

Eaton Power Defense 240V Max, Frame 3, Two Pole, 175A, 85kA/240V, 50C Cal T-M (Fxd-Adj) TU, No Terminals

Photo is representative

General specifications

Product Name	Catalog Number
Eaton Power Defense molded case circuit breaker	PDD32K0175VFAN
	UPC
	786689301637
Product Length/Depth	Product Height
109.1 mm	257.1 mm
Product Width	Product Weight
138.9 mm	3.65 kg
Compliances	
RoHS Compliant	



Delivery program

Amperage Rating

175 A

Circuit breaker frame type

Complete breaker

Frame

3

Number of poles

Two-pole

General information

Circuit breaker type

PD3 Global

Class

Class A

Series

Power defense

Trip Type

T-M (Fxd-Adj) TU

Other

Calibration

50C Calibration

Technical data - Electrical

Voltage rating

240 V AC

Voltage rating - max

240 V

Technical data - Mechanical - Terminals

Terminals

No Terminals

Technical information

Interrupt rating

85 kAIC at 240 Vac

Resources

Brochures

[StrandAble terminals product aid](#)

[Power Defense brochure](#)

Certification reports

[PDG3 UL authorization 250-600a TMTU](#)

[Power Defense Declaration concerning California's Proposition 65](#)

[PDG3 UL authorization 100-400a](#)

Multimedia

[Power Defense Frame 5 Trip Unit How-To Video](#)

[Power Defense Breakers](#)

[Power Defense Frame 3 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Frame 2 Variable Depth Rotary Handle Mechanism Installation How-To Video](#)

[Power Defense Frame 6 Trip Unit How-To Video](#)

[Power Defense molded case circuit breakers](#)

[Eaton Power Defense for superior arc flash safety](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - PDD32K0175VFAN](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)