

Eaton Q18S3R-A7

Catalog Number: Q18S3R-A7

RMQ-16 Keyed Selector Switch, 18 mm, Three-position, Left momentary, right maintained, Key removal center, Color: Black, Non-illuminated, IP65, Operating cycle: 3 million operations

General specifications



Photo is representative

Product Name

Eaton RMQ 16 modular pushbutton

Catalog Number

Q18S3R-A7

EAN

4015080723219

Product Length/Depth

2.72 in

Product Height

0.71 in

Product Width

0.71 in

Product Weight

0.02 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

DIN VDE 0600

Certifications

UL Listed
CSA Certified
IEC 60947-5
EN 60947-5

Catalog Notes

VS Anti-rotation feature

Type

Selector switch

Face plate size

18 x 18 mm

Key removal position

Key removal center

Operating Cycles

3 million operations

Actuator function

Left momentary, right maintained

Button color

Black

Actuator

Key operated

Size

16.2 mm

Environmental rating

IP65

Illumination

Non-illuminated

Number of positions

3

Series

RMQ-16

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - Q18S3R-A7](#)