

Eaton Q25D-X

Catalog Number: Q25D-X

RMQ-16 Non-illuminated Pushbutton, 25 mm, Momentary, Color: No button plate, Non-illuminated, IP65, Operating cycle: 3 million operations

General specifications



Photo is representative

Product Name

Eaton RMQ 16 modular pushbutton

EAN

4015080936244

Product Height

0.98 in

Product Weight

0.02 lb

Compliances

DIN VDE 0600

Catalog Number

Q25D-X

Product Length/Depth

1.97 in

Product Width

0.98 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

IEC 60947-5

UL Listed

EN 60947-5

CSA Certified

Type

Modular pushbutton

Actuator function

Momentary

Button color

Not applicable

Actuator

Button

Illumination

Non-illuminated

Series

RMQ-16

Environmental rating

IP65

Face plate size

25 x 25 mm

Operating cycles

3 million

Size

16.2 mm

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - Q25D-X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)