

Eaton Q25LTR-GN{WB}

Catalog Number: Q25LTR-GN/WB

Eaton RMQ 16 modular pushbutton, 25 mm, Maintained, Color: Green, Incandescent 24V, Illuminated, IP65, Operating cycle: 3 million operations

General specifications



Photo is representative

Product Name

Eaton RMQ 16 modular pushbutton

Catalog Number

Q25LTR-GN/WB

EAN

4015080863809

Product Length/Depth

2.36 in

Product Height

0.98 in

Product Width

0.98 in

Product Weight

0.01 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

DIN VDE 0600

Certifications

CSA Certified
IEC 60947-5
EN 60947-5
UL Listed

defaultTaxonomyAttributeLabel

Application

Pushbutton

Special features

Q25 series

Type

16.2 mm RMQ-16

Actuator color

Green

Actuator function

Maintained

Button color

Green

Actuator

Flush

Illumination

Illuminated

Series

RMQ-16

Environmental rating

IP65

Face plate size

25 x 25 mm

Light unit type

Incandescent 24V

Operating cycles

3 million

Size

16.2 mm

Resources

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Specifications and datasheets

[Eaton Specification Sheet - Q25LTR-GN/WB](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)