

Eaton RFTR9605-TGY

Catalog Number: RFTR9605-TGY

Eaton Z-Wave plus split control wireless receptacle, Tamper resistant, 15A, Residential, Flush mounting, 120V, Wire leads, Push button actuator, 60 Hz, Thermoplastic, Gray, 5-15R, Two-pole, Three-wire, grounding, Decorator



General specifications

Product Name	Catalog Number
Eaton Z-Wave Plus Split control wireless receptacle	RFTR9605-TGY
	UPC
	032664758737
Product Length/Depth	Product Height
1.39 in	4.2 in
Product Width	Product Weight
1.61 in	0.3 lb
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Special features

Tamper Resistant Receptacle

Type

Split control, duplex

Amperage Rating

15A

Voltage rating

120 V

Application

Residential

Wiring method

Wire leads

Actuator

Pushbutton

Frequency rating

60 Hz

Material

Thermoplastic

NEMA configuration

5-15R

Number of wires

3

Grounding

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Color

Gray

Resources

Multimedia

[Eaton's new Z-Wave Plus wireless collection](#)

Specifications and datasheets

[Eaton Specification Sheet - RFTR9605-TGY](#)

[Z-Wave Plus wireless duplex receptacle spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)