

Eaton RFTR9605-TWS

Catalog Number: RFTR9605-TWS

Eaton Z-Wave plus split control wireless receptacle, Tamper resistant, 15A, Residential, Flush mounting, 120V, Wire leads, Push button actuator, 60 Hz, Thermoplastic, White satin, 5-15R, Two-pole, Three-wire, grounding, Decorator



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Z-Wave Plus Split control wireless receptacle	RFTR9605-TWS
	UPC
	032664758744
Product Length/Depth	Product Height
1.39 in	4.2 in
Product Width	Product Weight
1.61 in	0.3 lb
Certifications	
cULus Listed	

defaultTaxonomyAttributeLabel

Special features

Tamper Resistant Receptacle

Type

Split control, duplex

Amperage Rating

15A

Voltage rating

120 V

Application

Residential

Wiring method

Wire leads

Actuator

Pushbutton

Frequency rating

60 Hz

Material

Thermoplastic

NEMA configuration

5-15R

Number of wires

Grounding

3

Mounting method

Flush

Number Of Poles

Two-pole

Style type

Decorator

Color

White satin

Resources

Multimedia

[Eaton's new Z-Wave Plus wireless collection](#)

Specifications and datasheets

[Eaton Specification Sheet - RFTR9605-TWS](#)

[Z-Wave Plus wireless duplex receptacle spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)