

Eaton RMSBP424

Catalog Number: RMSBP424

Instant Service Switchboard, Main Fused Switch, With Distribution Panel, 400A main ampere rating, Three-phase, Four-wire, NEMA 3R (Outdoor), 240V max., double branch provisions for 4 Type ED 225A frame and 24 poles of Type BAB 100A frame



Photo is representative

General specifications

Product Name	Catalog Number
Eaton instant switchboard meter main	RMSBP424
UPC	Product Length/Depth
782114653715	26 in
Product Height	Product Width
90 in	38 in
Product Weight	Warranty
750 lb	1 year
Compliances	Certifications
EUSERC Approved	UL Listed
Meets UBC, CBC, and IBC requirements for all seismic zones	Catalog Notes
	240V distribution panels have double branch provisions for four Type ED 225A frame circuit breakers and 24 poles of Type BAB 100A frame circuit breakers

defaultTaxonomyAttributeLabel

Type

Main Fused Switch with Distribution Panel

Amperage Rating

400A

Phase

Three-phase

Enclosure

NEMA 3R

Number of wires

4

Voltage - max

240 V

Resources

Brochures

[Distribution switchboards](#)

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Drawings

[Instant Service Switchboard Drawings - Main and Distribution Panel](#)

Specifications and datasheets

[Switchboards—Low Voltage](#)

[Eaton Specification Sheet - RMSBP424](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)