

Eaton RT20P11F3716CU

Catalog Number: RT20P11F3716CU

Eaton General purpose ventilated transformer, Marine-duty, DS-3 (1-phase), PV 240 x 480V, Taps: 1 at +5%/2 at -5% x 2 at +2.5%/4 at -2.5%, SV 120/240V, 115°C rise, 37.5 kVA, 16, Copper windings



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose ventilated transformer	RT20P11F3716CU
	UPC
	786680207044
Product Length/Depth	Product Height
20.36 in	37.59 in
Product Width	Product Weight
22.87 in	450 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	ABS Certified
	Catalog Notes
	DOE 2016 Efficient

Physical Attributes

Coil material

Copper

Enclosure

NEMA 2

Frame

818

Tap size

1 at +5% FCAN, 2 at -5% FCBN x 2 at 2.5% FCAN, 4 at -2.5% FCBN

Type

Marine Duty Transformer

Performance Ratings

Frequency rating

60 Hz

Primary voltage

240 x 480 V

Secondary Voltage

120/240 V

Volt ampere rating

37.5 kVA

Miscellaneous

Weathershield

WS11

Resources

Specifications and datasheets

[Eaton Specification Sheet - RT20P11F3716CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)