

Eaton S10N04B02PCUS6

Catalog Number: S10N04B02PCUS6

Encapsulated Transformer, EP, Single-phase, 120V X 240V, No Taps, 12/24V, 80, 2 kVA, Copper windings, Frame 68P, Wiring diagram 3B, 60 Hz, 1 K factor, NEMA 3R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S10N04B02PCUS6
	UPC
	786680099861
Product Length/Depth	Product Height
6.32 in	13.78 in
Product Width	Product Weight
6 in	1 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CSA Certified
	Catalog Notes
	316SS ENCLOSURE

Physical Attributes

Enclosure

NEMA 3R

Frame

Frame 68P

Tap size

No Taps

Type

Encapsulated transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

12/24 V

Temperature rise

80 °C rise

Volt ampere rating

2

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S10N04B02PCU56](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia