

Eaton S10N06A01S6

Catalog Number: S10N06A01S6

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 59A, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 3C



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S10N06A01S6
	UPC
	786680087806
Product Length/Depth	Product Height
5.75 in	11.28 in
Product Width	Product Weight
5.99 in	28 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Grade 316 stainless steel enclosure

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

59A

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3C

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

16/32 V

Temperature rise

115 °C rise

Volt ampere rating

1 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S10N06A01S6](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)