

Eaton S10N06A03X

Catalog Number: S10N06A03X

General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 16/32V, 115°C, 3 kVA, Aluminium windings, Frame: 177, Indoor-Outdoor

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S10N06A03X
	UPC
	786680094118
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	118 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	50/60 Hz

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

177

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

509B

Performance Ratings

Frequency rating

50-60 Hz

Phase

Single-phase

Primary voltage

120 V, 240 V

Secondary Voltage

16/32 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S10N06A03X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)