

Eaton S18N11E05

Catalog Number: S18N11E05

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 177, 60 Hz, single-phase, 208 V, 416 V, 120/240 V, NONE, 115 °C rise, 5 KVA, indoor-outdoor, 3Q



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S18N11E05
	UPC
	786680060564
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	120 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

177

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

3Q

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

208 V, 416 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S18N11E05



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)