

Eaton S19-SP

Catalog Number: S19-SP

Eaton Arrow Hart extra heavy-duty angled plug , #10-8 AWG, 60A, Commercial|range & dryer, 120/208V, Back wire, Black, Brass, PVC, 18-60P, Four-pole, four-wire, non grounding, Screw, 1.00", Thermoplastic, Retail Box

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Arrow Hart extra heavy-duty angled plug	S19-SP
	UPC
	032664197604
Product Length/Depth	Product Height
8 in	3 in
Product Width	Product Weight
6 in	0.455 lb
Certifications	
UL Listed	

defaultTaxonomyAttributeLabel

Device type

Plug

Special features

Non-grounding

Type

Angled plug

Amperage Rating

60A

Voltage rating

120/208 V

Contact material

Brass

Features

Non-grounding

Application

Commercial, range and dryer

Device grade

Extra heavy-duty industrial specification grade

Wiring method

Back wire

Number of wires

4

Number Of Poles

Four-pole

Style type

Power, Universal angled body

Cord range

1.00"

Material

Thermoplastic

Packaging type

Retail Box

Color

Black

Resources

Brochures

[Flush mount receptacles sell sheet](#)

Catalogs

[Arrow Hart Buyers Guide Section B](#)

Specifications and datasheets

[Eaton Specification Sheet - S19-SP](#)

Connection type

Screw

Allowable wire size

#10-8 AWG

NEMA configuration

18-60P

Torque rating

20 lbf-inch

Design type

Straight blade

Face/body material

PVC

Receptacle type

Four-pole, four-wire, non grounding



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)