

# Eaton S20L11S05CULS42

Catalog Number: S20L11S05CULS42

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 177, 60 Hz, single-phase, 240 V, 480 V, 120/240 V, 2 at-5% FCBN x 4 at -2.5% FCBN, 115 °C rise, 5 KVA, indoor-outdoor, 23A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20L11S05CULS42
	<b>UPC</b>
	786680103926
<b>Product Length/Depth</b>	<b>Product Height</b>
9.89 in	16 in
<b>Product Width</b>	<b>Product Weight</b>
10.38 in	117 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	<b>Catalog Notes</b>
	Low sound design equivalent to 42 dB

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

177

### Tap size

2 at -5% FCBN x 4 at -2.5% FCBN

### Type

General-purpose encapsulated transformer

### Wiring connection

23A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

5 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S20L11S05CULS42

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)