

Eaton S20L11S07CULS42

Catalog Number: S20L11S07CULS42

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 178, 60 Hz, low sound 42 dB, single-phase, 240 V, 480 V, 120/240 V, 2 at -5% FCBN X 4 at -2.5% FCBN, 115 °C rise, 7.5 KVA, indoor-outdoor, 23A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20L11S07CULS42
	UPC
	786680083174
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	138 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	Low sound equal to 42 dB

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

178

Tap size

2 at -5% FCBN x 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

23A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

7.5 kVA

Miscellaneous

Modification 1

Low sound 42 dB

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S20L11S07CULS42



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)