

Eaton S20L11S25CU

Catalog Number: S20L11S25CU

Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 240 x 480V, Taps: 2 at-5% FCBN x 4 at -2.5% FCBN, SV: 120/240V, 115°C, 25 kVA, Copper windings, Frame: 182, 23A, Indoor-Outdoor, 60 Hz, NEMA 3R



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20L11S25CU
	UPC
	786680104077
Product Length/Depth	Product Height
14.12 in	23.31 in
Product Width	Product Weight
16.35 in	380 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

182

Tap size

2 at -5% FCBN x 4 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

23A

Performance Ratings

Frequency rating

60 Hz

Kva Rating

25 kVA

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

25 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S20L11S25CU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)