

Eaton S20L11S37CU

Catalog Number: S20L11S37CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 300A, 60 Hz, single-phase, 240 V, 480 V, 120/240 V, 2 at -5% FCBN X 4 at -2.5% FCBN, 115 °C rise, 37.5 KVA, indoor-outdoor, 248A



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20L11S37CU
	UPC
	786680015953
Product Length/Depth	Product Height
14.06 in	28.24 in
Product Width	Product Weight
22.42 in	867 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

300A

Tap size

2 at -5% FCBN x 4 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

248A

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

37.5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

Eaton's Volume 2—Commercial Distribution

Specifications and datasheets

Eaton Specification Sheet - S20L11S37CU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia