

# Eaton S20N11B25CU

Catalog Number: S20N11B25CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 182, 60 Hz, single-phase, 240 V, 480 V, 120/240 V, 2 at -5% FCBN X 4 at -2.5% FCBN, 80 °C rise, 25 KVA, indoor-outdoor, 3A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11B25CU
	<b>UPC</b>
	786680048081
<b>Product Length/Depth</b>	<b>Product Height</b>
14.12 in	23.31 in
<b>Product Width</b>	<b>Product Weight</b>
16.35 in	430 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

182

### Tap size

2 at -5% FCBN x 4 at -2.5% FCBN

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

80 °C rise

### Volt ampere rating

25 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S20N11B25CU



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia