

# Eaton S20N11E01X

Catalog Number: S20N11E01X

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 67, 50-60 Hz, single-phase, 240 V, 480 V, 120/240 V, NONE, 115 °C rise, 1 KVA, indoor-outdoor, 90A

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11E01X
	<b>UPC</b>
	786680018251
<b>Product Length/Depth</b>	<b>Product Height</b>
6.52 in	13.41 in
<b>Product Width</b>	<b>Product Weight</b>
6.37 in	0.001 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	50/60 Hz

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

67

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

90A

## Performance Ratings

### Frequency rating

50-60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

1 kVA

## Miscellaneous

### Special features

Electrostatically shielded

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S20N11E01X



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)