

# Eaton S20N11E15CUSS

Catalog Number: S20N11E15CUSS

Eaton, general purpose encapsulated transformer, ep, single-phase, primary voltage: 240 x 480v, taps: none, secondary voltage: 120/240v, 115°C, 15 kva, copper windings, fr180, 90a, indoor-outdoor, electrostatically shielded, 60 hz, nema 3r.



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11E15CUSS
	<b>UPC</b>
	786680104039
<b>Product Length/Depth</b>	<b>Product Height</b>
10.52 in	19 in
<b>Product Width</b>	<b>Product Weight</b>
13.38 in	311 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	<b>Catalog Notes</b>
	Grade 304 Stainless Steel Enclosure

## Physical Attributes

### Coil material

Copper

### Design

EP

### Enclosure

NEMA 3R

### Frame

180

### Tap size

None

### Type

General-purpose encapsulated transformer

### Wiring connection

90A

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

15 kVA

## Miscellaneous

### Special features

Electrostatically shielded

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Specifications and datasheets

Eaton Specification Sheet - S20N11E15CUSS

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)