

Eaton S20N11S03CUS64X

Catalog Number: S20N11S03CUS64X

Eaton, general purpose encapsulated transformer, ep single-phase 240 x 480v none 120/240v 115°C 3 kva copper windings 1764x 3a indoor-outdoor 60 hz nema 4x



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S20N11S03CUS64X
	UPC
	786680116483
Product Length/Depth	Product Height
8 in	14.25 in
Product Width	Product Weight
7.69 in	0.001 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	NEMA 4X Grade 316 stainless steel enclosure.

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 4X

Frame

1764X

Tap size

None

Type

General-purpose encapsulated transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

3 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S20N11S03CUS64X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)