

# Eaton S20N11S05SS4X

Catalog Number: S20N11S05SS4X

Eaton General-Purpose Encapsulated Transformer, Single-phase, PV: 240 x 480V, Taps: None, SV: 120/240V, 115°C rise, 5 kVA, Al windings, Indoor-Outdoor, 304SS NEMA 4X enclosure



Photo is representative

## General specifications

### Product Name

Eaton General purpose encapsulated transformer

### Catalog Number

S20N11S05SS4X

### UPC

786680064562

### Product Length/Depth

9.5 in

### Product Height

14.6 in

### Product Width

13.88 in

### Product Weight

116 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year NAFTA from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

### Certifications

UL Listed

### Catalog Notes

Grade 304 stainless steel enclosure with NEMA 4X rating

## Physical Attributes

### Coil material

Aluminum

### Enclosure

NEMA 3R

### Frame

1774X

### Insulation

180 °C

### Mounting

Wall

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

60 Hz

### Kva Rating

15 kVA

### kVA

5 kVA

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Sound Level

NEMA ST-20

### Temperature rise

115 °C rise

### Volt ampere rating

5 kVA

## Miscellaneous

### Special features

NEMA 4X Enclosure 304SS

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S20N11S05SS4X](#)