

Eaton S20N11S07SS4X

Catalog Number: S20N11S07SS4X

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 60 Hz, single-phase, 240 V, 480 V, 120/240 V, NONE, 115 °C rise, 7.5 KVA, indoor-outdoor



Photo is representative

General specifications

Product Name

Eaton General purpose encapsulated transformer

Catalog Number

S20N11S07SS4X

UPC

786680083945

Product Length/Depth

0.001 in

Product Height

0.001 in

Product Width

0.001 in

Product Weight

0.001 lb

Warranty

Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

Catalog Notes

Grade 304 stainless steel enclosure with NEMA 4X rating

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Tap size

None

Type

General-Purpose Encapsulated Transformer

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V, 480 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

7.5 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S20N11S07SS4X](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)