

# Eaton S20N11S25X

Catalog Number: S20N11S25X

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 182, 50-60 Hz, single-phase, 240 V, 480 V, 120/240 V, NONE, 115 °C rise, 25 KVA, indoor-outdoor, 3A



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S20N11S25X
	<b>UPC</b>
	786680080852
<b>Product Length/Depth</b>	<b>Product Height</b>
14.12 in	23.31 in
<b>Product Width</b>	<b>Product Weight</b>
16.35 in	398 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	<b>Catalog Notes</b>
	50/60 Hz

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

182

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

3A

## Performance Ratings

### Frequency rating

50-60 Hz

### Phase

Single-phase

### Primary voltage

240 V, 480 V

### Secondary Voltage

120/240 V

### Temperature rise

115 °C rise

### Volt ampere rating

25 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S20N11S25X](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)