

# Eaton S23N15S07X

Catalog Number: S23N15S07X

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 179, 50-60 Hz, single-phase, 230 V, 115 V, NONE, 115 °C rise, 7.5 KVA, indoor-outdoor, 511AV



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S23N15S07X
	UPC
	786680097492
<b>Product Length/Depth</b>	<b>Product Height</b>
10.52 in	19 in
<b>Product Width</b>	<b>Product Weight</b>
13.38 in	197 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	50/60 Hz

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Enclosure

NEMA 3R

### Frame

179

### Tap size

None

### Type

General-Purpose Encapsulated Transformer

### Wiring connection

511AV

## Performance Ratings

### Frequency rating

50-60 Hz

### Phase

Single-phase

### Primary voltage

230 V

### Secondary Voltage

115 V

### Temperature rise

115 °C rise

### Volt ampere rating

7.5 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S23N15S07X](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)