

Eaton S24N12P02P

Catalog Number: S24N12P02P

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 68P, 60 Hz, single-phase, 240 V, 120 V, None, 115 °C rise, 2 KVA, indoor-outdoor, 511AJ

General specifications



Photo is representative

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S24N12P02P
	UPC
	786680103780

Product Length/Depth	Product Height
6.32 in	13.78 in

Product Width	Product Weight
6 in	42 lb

Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year CSA Certified from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	UL Listed
	Catalog Notes
	EP and EPT on New Resin (135°C Rise)

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

68P

Tap size

None

Type

General-purpose encapsulated transformer

Wiring connection

511AJ

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

240 V

Secondary Voltage

120 V

Temperature rise

115 °C rise

Volt ampere rating

2 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S24N12P02P](#)