

Eaton S25N11S10X

Catalog Number: S25N11S10X

Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 180, 50-60 Hz, single-phase, 220 V, 120/240 V, NONE, 115 °C rise, 10 KVA, indoor-outdoor, 26D



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S25N11S10X
	UPC
	786680097515
Product Length/Depth	Product Height
10.52 in	19 in
Product Width	Product Weight
13.38 in	200 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Catalog Notes
	50/60 Hz

Physical Attributes

Coil material

Aluminum

Design

EP

Enclosure

NEMA 3R

Frame

180

Tap size

None

Type

General-Purpose Encapsulated Transformer

Wiring connection

26D

Performance Ratings

Frequency rating

50-60 Hz

Phase

Single-phase

Primary voltage

220 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

10 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S25N11S10X](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)