

# Eaton S25N27S05

Catalog Number: S25N27S05

Eaton General purpose encapsulated transformer, EP, aluminum, 177, 60 Hz, single-phase, 220 V, 277 V, None, 115 °C rise, 5 KVA, indoor-outdoor, 519AA



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton General purpose encapsulated transformer	S25N27S05
	<b>UPC</b>
	786680112355
<b>Product Length/Depth</b>	<b>Product Height</b>
9.89 in	16 in
<b>Product Width</b>	<b>Product Weight</b>
10.38 in	139 lb
<b>Warranty</b>	<b>Certifications</b>
Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

## Physical Attributes

### Coil material

Aluminum

### Design

EP

### Frame

177

### Tap size

None

### Type

General-purpose encapsulated transformer

### Wiring connection

519AA

## Performance Ratings

### Frequency rating

60 Hz

### Phase

Single-phase

### Primary voltage

220 V

### Secondary Voltage

277 V

### Temperature rise

115 °C rise

### Volt ampere rating

5 kVA

## Miscellaneous

### Weathershield

Indoor-Outdoor

## Resources

### Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

### Specifications and datasheets

[Eaton Specification Sheet - S25N27S05](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)