

Eaton S27D11E05CU

Catalog Number: S27D11E05CU

Eaton General purpose encapsulated transformer, EP, copper, NEMA 3R, 177, 60 Hz, single-phase, 277 V, 120/240 V, 2 at +2.5% FCAN, 2 at -2.5% FCBN, 115 °C rise, 5 KVA, indoor-outdoor, 539K



Photo is representative

General specifications

Product Name	Catalog Number
Eaton General purpose encapsulated transformer	S27D11E05CU
	UPC
	786680094132
Product Length/Depth	Product Height
9.89 in	16 in
Product Width	Product Weight
10.38 in	120 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

Physical Attributes

Coil material

Copper

Design

EP

Enclosure

NEMA 3R

Frame

177

Tap size

2 at +2.5% FCAN, 2 at -2.5% FCBN

Type

General-Purpose Encapsulated Transformer

Wiring connection

539K

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

277 V

Secondary Voltage

120/240 V

Temperature rise

115 °C rise

Volt ampere rating

5 kVA

Miscellaneous

Special features

Electrostatically shielded

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S27D11E05CU](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)