

Eaton S27D12P01P

Catalog Number: S27D12P01P

Eaton General purpose encapsulated transformer, EP, copper, 67P, 60 Hz, single-phase, 277 V, 120 V, 2 at +2.5% FCAN 2 at -2.5% FCBN, 115 °C rise, 1 KVA, indoor-outdoor, 16AK



Photo is representative

General specifications

| Product Name | Catalog Number |
|---|----------------|
| Eaton General purpose encapsulated transformer | S27D12P01P |
| | UPC |
| | 786680112225 |
| Product Length/Depth | Product Height |
| 0.001 in | 0.001 in |
| Product Width | Product Weight |
| 0.001 in | 32 lb |
| Warranty | Certifications |
| Eaton Selling Policy 25-000, one (1) year Contact Manufacturer from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first. | |

Physical Attributes

Coil material

Copper

Design

EP

Frame

67P

Tap size

2 at +2.5% FCAN 2 at -2.5% FCBN

Type

General-purpose encapsulated transformer

Wiring connection

16AK

Performance Ratings

Frequency rating

60 Hz

Phase

Single-phase

Primary voltage

277 V

Secondary Voltage

120 V

Temperature rise

115 °C rise

Volt ampere rating

1 kVA

Miscellaneous

Weathershield

Indoor-Outdoor

Resources

Catalogs

[Eaton's Volume 2—Commercial Distribution](#)

Specifications and datasheets

[Eaton Specification Sheet - S27D12P01P](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)